



# DISPOSABLE WIPE DISPENSER + Premium Disposable Wipes

## REUSABLE, HEAVY-DUTY CONTAINER

Bucket, lid and star-dispensing insert are made with closed-cell co-polymer material which is rust-proof and resistant to mold, mildew and bacteria. Easy to clean with rounded corners and no sharp corners.

## PREMIUM DISPOSABLE WIPES

Disposable wipes are more like heavy-duty towels! These non-woven, dry wipes are ready for charging with your choice of solution and have indefinite shelf life. Extra large 11" x 12.5" size for larger area cleaning.

## UNIQUE SNAP-N-SEAL TOP

Cover has sliding Snap-n-Seal feeder top which is easy to operate and snaps to seal out air, keeping wipes moist and ready-to-use.

## COMPLETELY PORTABLE

Sturdy handle makes it completely portable. Fits on the Alpha ES Workstation cleaning cart for transport, then carry it to the exact location where cleaning is needed.

## USE WITH VARIETY OF WIPES

Can be used with other pre-moistened wipes packaged in similar size.



Internal dimensions:  
7.85" W x 4.7" D x 7.85" H

External dimensions:  
8" W x 5" D x 8" H

# ABOUT FILMOP DISPOSABLE-WIPE CHARGING/DISPENSING BUCKET

## SIMPLE TO USE



Place Filmop Disposable Wipes in Charging/Dispensing bucket.



Fill bucket with solution of your choice (2-3 quarts recommended for single roll).




Pull single wipe from the center of the roll.



Pull center wipe through star-shaped insert to begin usage.

## SNAP-N-SEAL TOP



Heavy-duty star-shaped insert feeds wipes through cover. As charged wipes are pulled through it, the heavy-duty fins squeeze excess liquid to eliminate wasteful dripping and provide a perfectly saturated wipe. To seal, slide the black Snap-n-Seal top to closed position. Wipes stay moist and ready-to-use.

## FILMOP NON-WOVEN DISPOSABLE WIPES



Filmop's premium disposable wipes are non-woven (a blend of 65% viscose, 35% polyester) and measure a generous 11" x 12.5". They are packaged dry so they have an indefinite shelf life and allow you to use the solution of your choice.

**A non-woven wipe releases an average of 90% of the original concentration of quaternary ammonium solution after 8 hours compared to a cellulose-based wipe which releases only 21% of the original concentration.**

~ KD MacDougall, C Morris, "Optimizing Disinfectant Application in Healthcare Facilities," *Infection Control Today*, 2006

| PRODUCT (S)   | ITEM #      | DESCRIPTION   | Unit of Measure | Case Pack |
|---|-------------|---|-----------------|-----------|
|  | 0000SE3104A | 1 gallon REUSABLE DISPOSABLE WIPE DISPENSER (FOR CHARGING OR DISPENSING DISPOSABLE WIPES), BLUE. HEAVY-DUTY CO-POLYMER WITH SNAP-LOCK DISPENSING OPENING. CAN BE USED FOR CHARGING DRY DISPOSABLE WIPES, [ ITEM# 00PN0203000] OR DISPENSING PRE-MOISTENING PACKAGED WIPES. Internal dimensions: 7.85" W x 4.7" D x 7.85" H. External dimensions: 8" W x 5" D x 8" H | case            | 1         |
|  | 00PU0203000 | 11" x 12.5" DISPOSABLE WIPES, NON-WOVEN, 65% VISCOSE / 35% POLYESTER. 1 Roll, pulls from the CENTER. (6 rolls / 90 wipes per roll = 540 wipes per case). Roll size: 7.87"x 5.3 x 5.5" (wipes are folded in half for packaging).   | case            | 6         |